



# Control & Instrumentation

To help in selecting the most suitable equipment for your application, the operating characteristics of our ovens and furnaces are shown on their product bulletins. This bulletin more completely defines and explains these operating characteristics and their use as a guideline for equipment selection.

## ● Control Accuracy

Temperature controllers have many different accuracy ratings for features such as set point, display, repeatability and calibration. For the purpose of our product bulletins, we have defined control accuracy as the ability of the temperature controller to maintain a constant temperature, by altering heat input, at the point in the equipment where the temperature is being sensed. For this reason, we have chosen the manufacturer's published accuracy rating of the temperature controller that would most affect the stability of temperature at this sensing point.

Product bulletins for equipment using non-electronic temperature controllers such as bi-metallic or fluid filled thermostats, list the control accuracy in degrees. In these cases, the control accuracy gives an indication of the maximum amount of cyclic variation which could be seen at the sensing point

For electronic temperature controllers, the control accuracy on the product bulletins is shown as a percent of the span and is a comparison of the temperature at the sensing point to a calibration source. The span of the temperature controllers is typically 900°F, 1600°F or 2400°F, depending on the maximum

## ● Temperature Uniformity

Temperature uniformity is listed in degrees. This is a measurement of the distribution of heat within the oven work space. This data is the result of actual tests run in a stabilized empty oven with a minimum of nine thermocouples—eight thermocouples located at the corners of the work space and one in the center of the work space. The corner thermocouples are placed 2" to 12" from the work space edges (based on the size of the equipment) to be representative of the useable work space. Temperature uniformity will normally improve as the operating temperature is lowered. Other factors may affect temperature uniformity adversely.

Blocking the air flow within the work space will adversely affect the distribution of heated air and, therefore, the temperature uniformity. Care must be taken to pick equipment with a recirculated air flow pattern suited to the product loading.

Temperature uniformity tests have been run with minimal exhaust from the equipment. Heat input that is required to offset a large

## ● Rise Time

The time required to heat oven air to set point (rise time) is a measure of available heat input and an indication of how fast an oven may heat up. The rise time information is based on actual tests measuring the time required for temperature at the sensing point to rise from room temperature to set point.

The rise time tests were run with an empty oven and a minimum exhaust rate. Lower than design voltage on electric equipment or insufficient gas pressure on gas equipment will reduce heat input and increase rise time. Increased exhaust or heavy loads will also increase the time required to rise to set temperature.

Initially, it is necessary to heat up internal steel and insulation that surrounds the work space. Once the equipment reaches the set



operating temperature of the equipment. In most instances, the temperature fluctuation due to the electronic temperature controller is dwarfed by other system characteristics affecting temperature uniformity such as loading, exhaust rate and available heat input.

Equipment with heat input most closely sized to requirements will show the least fluctuation at the sensing point. Very large heat input (most often encountered in gas or steam heated equipment), can result in a large addition of heat input to the system before the temperature controller can react. This effect is minimized in gas and steam heated equipment by modulating the heat input rather than turning it on and off. Electric ovens with large heat input can minimize this effect by the installation of an SCR power controller. See the reverse side of this bulletin for additional information.

Temperature controller accuracy is based on tests performed by the temperature controller manufacturer with published results. This is only one of the many specifications published by the temperature controller manufacturer. Complete temperature controller specifications are available upon request.

exhaust rate can be compensated for by increasing heat input. However, a large exhaust rate can have a detrimental effect on temperature uniformity. Hot air exhausted must be replaced with cooler fresh air. The fresh air is heated by being recirculated through the heat source. The larger the exhaust rate, the less the fresh air is mixed before being exhausted. This will result in non-uniform temperatures in the recirculated air flow.

If tight temperature uniformity is required with a large exhaust rate, it may be necessary to increase the size of the recirculating blower in the equipment. Those applications which will require large exhaust rates should be discussed with our sales engineers.

In furnaces, where the heat transfer is by radiant heat, high temperature fans can be added to the equipment or the heating elements zoned within the work space to improve temperature uniformity. These applications should be discussed with a factory sales engineer.

temperature, additional time is required to stabilize temperatures within the oven. During this stabilization period, the insulation is heated and the temperature profile through the insulated wall will reach a steady state. As this happens, the output of the heat source will reduce from maximum to the much smaller amount required to offset the loss through the insulated walls and exhaust.

While both a high exhaust rate and a large load will increase the time to reach set point and stabilize, only the exhaust rate will increase power consumption after stabilization. Once the load is stabilized, the power consumption will be the same as for an unloaded oven.

**On the reverse side of the Bulletin, we have provided additional details on our standard digital temperature controller as well as details on the optional controls listed on our Product Bulletins. Other brands or models of instrument are also available—contact one of our sales engineers.**

# SPECIFICATIONS

Instruments have been selected to provide a full range of features at an economical price. Consideration has also been given to selecting instruments that are easy to understand and use.

We can provide full installation and configuration of any other instrument. Also, alternate control arrangements such as remote or free standing control panels are available. Please contact our sales engineers in your area.

## STANDARD DIGITAL TEMPERATURE CONTROLLER

### PARTLOW 1400+

- **Digital Display**, two LED, alphanumeric, 4 digit displays; 0.53" high for temperature display and 0.39" high for set point display
- **Accuracy**,  $\pm 0.25\%$  of span plus 1 degree display error



## PROGRAMMABLE TEMPERATURE CONTROLLER

### WATLOW F4

- **Program Parameters**, 256 steps which can be programmed into as many as 40 nameable profiles, a real time clock can be used to start profiles at any time of day
- **Digital Display**, dual 0.63" high, LED, alphanumeric 5 digit display of process variables positioned above a user configurable, four line, high definition, LCD, interface display for aid in set-up, operation of controller, and programming
- **Accuracy**,  $\pm 0.1\%$  of span plus 1 degree display error



## RECORDING THERMOMETER

### PARTLOW MRC 5000

- **Record**, 10" diameter circular chart  
24 hour chart rotation (others available)
- **Digital Display**, 0.56" high, LED, alphanumeric, 4 digit display;  
LED status display
- **Accuracy**,  $\pm 0.25\%$  of span plus 1 degree display error



## PROGRAMMABLE RECORDING TEMPERATURE CONTROLLER

### PARTLOW MRC 7000

- **Program Parameters**, 8 programs of 6 ramp and soak segments which can be combined for larger programs
- **Record**, 10" diameter circular chart  
User configurable chart range and chart rotation
- **Digital Display**, 0.56" high, LED, alphanumeric, 4 digit display;  
LED status display
- **Accuracy**,  $\pm 0.25\%$  of reading plus 1 degree display error



## SCR POWER CONTROLLER

Silicon controlled rectifier power controllers are completely solid state industrial controllers that insure precise proportioning of electric power to the heating elements. Oven temperature is maintained smoothly and evenly over the entire temperature range of the unit. SCR power controllers minimize maintenance, as there are no moving parts or electrical contacts to wear out. Heating element fatigue is reduced since the elements do not cool between releases of electric power. Zero voltage firing, including the first one half cycle of voltage, minimizes radio frequency and electromagnetic interference. Transient voltage suppressor networks are included and the units are provided with protective fusing.



Ovens and Furnaces For Industry Since 1949  
**THE GRIEVE CORPORATION**

500 Hart Road, Round Lake, Illinois 60073-2898 USA  
(847) 546-8225 Fax: (847) 546-9210  
www.grievcorp.com email: sales@grievcorp.com

Specifications and descriptions above cover our standard and optional temperature controls in use at the time of printing. Selection of controls and specifications are subject to change without notice.

Specifications Subject to Change Without Notice  
Copyright The Grieve Corporation All Rights Reserved  
Printed in U.S.A. 6/07